

SKLOP 6: KROMATOGRFSKE KOLONE SUPELCO

Zap. št.	kolona za	Naziv kolone	Zahtevana Kat. št.	Proizvajalec	Dimenzija	predvidena letna količina
1	GC	24081 Supelco, SUPELCOWAX® 10 Capillary GC Column, L × I.D. 60 m × 0.25 mm, df 0.25 µm	SU-24081	Supelco	60 m × 0.25 mm, df 0.25 µm	1 kos
2	GC	SP-2380 Fused silica Capillary column 60m x 0,25mm x 0,2µm film thickness, T max: 275°C	24111	Supelco	60m x 0,25mm x 0,2µm film thickness	1 kos
3	GC	SP-2560 Fused silica Capillary column 100m x 0,25mm x 0,2µm film thickness, T max: 250°C	24056	Supelco	100m x 0,25mm x 0,2µm film thickness	1 kos
4	GC	SPB-5 Fused silica Capillary column 30m x 0,25mm x 0,25µm film thickness, T max: 320°C	24034	Supelco	30m x 0,25mm x 0,25µm film thickness	1 kos