

## SKLOP 3: KROMATOGRAFSKE KOLONE AGILENT TECHNOLOGIES

Datum: 30.3.2020

Zap. št.	kolona za	Naziv kolone	Kat. št.	Proizvajalec	Dimenzija	predvidena letna količina
1	GC	DB-WAX 30m x 0,32mm x 0,50µm Temperature limits: from 20°C to 240°C (250°C)	123-7033	Agilent Technologies	30m x 0,32mm x 0,50µm	1 kos
2	GC	HP-5 30m x 0,32mm x 0,25µm Temperature limits: from -60°C to 325°C (350°C)	19091J-413	Agilent Technologies	30m x 0,32mm x 0,25µm	1 kos
3	HPLC	Poroshell 120EC-C18	699975-302	Agilent	3.0 x 50 mm 2.7 micron	1 kos
4	HPLC	ZORBAX SB-C18	827700-902	Agilent	Rapid Resolution HT 2.1 x 50 mm 1.8 micron 600 Bar	2 kos